

COVER3KIT™ INSTRUCTIONS FOR USE

*It is important to review label instructions. Not to be used as a substitute.

STEP 1: DISINFECT

surfaceclean

- Before applying SurfaceAide™ XL, it is important to clean and disinfect with SurfaceClean™.
- Prior to applying, ensure surface is completely clean and free of dirt and grime.
- Hold container six to eight inches from surface to be treated. Spray area until it is uniformly covered with the solution. Allow product to coat the surface and remain wet for 3-5 minutes.
- Clean surface with a clean cloth, mop or sponge. The product will not leave grit or soap scum.
- Use for regular maintenance cleaning for SurfaceAide™ XL treated and untreated surfaces.

STEP 2: 24/7 ANTIMICROBIAL PROTECTION

surfaceaide^{XL}

- After disinfecting surface with SurfaceClean™, apply SurfaceAide™ XL.
- Spray entire area 4-6 inches from the surface making sure the surface is uniformly covered. Apply and then let stand until dry or let stand 3 minutes and wipe dry with cloth or sponge.
- If spotting occurs, wipe with moist cloth or sponge. Test for staining and color-fastness of fabrics and carpets by treating and drying a small, concealed area prior to application.
- When treating coarser substrates, more SurfaceAide™ XL antimicrobial may be required due to absorption.
- Dry carpet areas and surfaces before re-entry and dry articles before use.

*The above directions are for spray applications. Please refer to bottle label for dipping/soaking application.

STEP 1: 24/7 ANTIMICROBIAL PROTECTION FOR FABRICS

fabricaide

Preparation:

- Garments must be clean prior to application. If dirty, wash them prior to antimicrobial treatment.
- Application of FabricAide® must be done separately from normal washing. Do not mix with regular detergent.

Application:

- Pour 4 oz. of FabricAide® into final rinse water of the washing cycle. Do not use in conjunction with any other laundry products.
- For front loaders, pour into dispenser for final rinse cycle.
- Dry garments as usual.

**SURFACECLEAN™, SURFACEAIDE™ XL AND FABRICAIDE® ARE WATER BASED PRODUCTS.
STORE AT ROOM TEMPERATURE.**